



X2 control 10

10" HMI with iX runtime and CODESYS soft control

1024 × 600 pixel (16:9) TFT-LCD touch screen

1.5 GB application memory

Ethernet 2x100 Mbit

EtherCAT as standard

CODESYS control integrated

CE, FCC, KCC, UL approvals

DNV GL, KR, LR, ABS, CCS, BV, NK, RS marine approvals

Facts

General description

Part number	630001905
Life cycle status	Active
Warranty	2 year

Certifications

General	CE, FCC, KCC, UL 61010-2-201
Marine	KR, LR, ABS, BV, CCS, NK, DNV GL, RS
Safety	UL 61010-1, UL 61010-2-201, CAN/CSA-C22.2 No. 61010-1, CAN/CSA-C22.2 No. 61010-2-201

Mechanical

Mechanical size	292 x 194 x 52mm
	Panel Mount, VESA 75 x 75
	1million finger touch operations
Touch type	Resistive
Cut-out size	275 x 177mm
Weight	1.65 kg
Housing material	Powder-coated aluminum, Gray

Power

Input voltage	24 V DC (18 to 32 VDC) CE: The power supply must conform with the requirements according to IEC 60950 and IEC 61558-2-4. UL and cUL: The power supply must conform with the requirements for class II power supplies.
Power consumption (max)	21.6W
Input fuse	Internal DC fuse
CPU	i.MX6Quad, Quad ARM Cortex-A9 1.0GHz 1MBL2cache
RAM	2 GB
FLASH	2GB SSD(eMMC), 1.5GB free for application

Display

Size diagonal	10.1" diagonal
Resolution	1024x600 pixels
Backlight	LED Backlight
Backlight life time	50000 hours
Backlight brightness	500 cd/m2
Backlight dimming	Industrial Dimming
Display type	TFT-LCD with LED backlight

Softcontrol

Codesys runtime version	3.5
Codesys EtherCAT	Yes
Codesys Modbus Ethernet	Yes
Codesys Modbus RTU	Yes
CANopen	Yes
Non volatile variables	64 KB

Drivers

Digital IO

Digital output	2xDO Solid state relay, 0.5A@24VDC
----------------	------------------------------------

Serial communication

Number of serial ports	1 Port 9pin DSUB
Serial port 1	RS 232 (RTS/CTS)
Serial port 2	RS422/485
Serial port 3	RS485 (only if COM 2 is RS485)

Ethernet communication

Number of Ethernet ports	2
Ethernet port 1	1x10/100 Base-T (shielded RJ45)
Ethernet port 2	1x10/100 Base-T (shielded RJ45)
	2
	0.5 MBit
	0.5 MBit

Expansion interface

Expansion port	Yes, cIX expansion module
SD card	SD and SDHC
USB	2xUSB 2.0 500mA

Environmental

Operating temperature	-10°C to +60°C
Storage temperature	-20°C to +70°C
Shock	15g, half-sine, 11ms according to IEC60068-2-27
Vibration	1g, according to IEC 60068-2-6, Test Fc
Sealing front	IP65, NEMA 4X/ 12 and UL 50E Type 4X/ 12
Sealing back	IP20
Humidity	5% – 85% non-condensed

Lenze - LECOM A/B (5.6.0)
LS Industrial System - Glofa (5.3.0)
LS Industrial System - Master K (5.4.0)
Matsushita - MEWTOCOL-COM (5.9.2)
Mitsubishi Electric - Alpha2 (5.7.0)
Mitsubishi Electric - A-series (C24) (5.6.0)

ers ▼

[Barcode scanner USB - iX script module \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[FTP Client - iX sample \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Log custom debug messages - iX sample \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[BFI-P2/H3 and X2 Control by Modbus TCP \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[BFI-P2/H3/E3 and X2 Control by Modbus RTU \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
modbus-rtu?
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[BFI-P2/E3 and X2 Control by CANopen \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Conveyor product tracking - CODESYS library \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
library?

[Fast logging - CODESYS library \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Recipes with pictures - iX sample \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[BFI-E3 and X2 Control by Modbus TCP \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Execute external SQL queries from file \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Vessel central dimming - iX sample \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Excel basic process data template \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Scheduler online editor - iX script module \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
module?

[Get NIC information - CODESYS library \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[OEE calculation example \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Custom recipe - iX script module \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[MJPEG graphical control - iX application \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Password expire - iX script module \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[SoftMotion library with X2 control - CODESYS library \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
codesys-library?
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Setting up projects for Energy Meter \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[iX file browser \(https://smartstore.beijerelectronics.com/en/Smart_Engineering_R...\)](#)
hstc=133514769.4931d322ad38576815e60802e8ae6d22.1682440547395.1683236169949.16

[Resources/9999/power-bi-basic-process-data-template?_ga=2.146652.68.1686247146652&_hsfp=2393331666](#)