

Professionally approved products.

## Datasheet

# 25 mm Steel Interchangeable Screwdriver

RS Stock number [213-0923](#)



### Features

Blade Finish: Sandblasted  
 Blade Length: 25 mm  
 Blade Material: S2 Steel  
 Screwdriver Type: Interchangeable

### Tip Size

Slotted: 3; 4; 5; 6; 7 mm;  
 Pozidriv: PZ0; PZ1; PZ2; PZ3;  
 Phillips: PH0; PH1; PH2; PH3;  
 Hexagon: 2; 2.5; 3; 4; 5; 6; 7 mm;  
 Torx: T10; T15; T20; T25; T30; T40

### Description

- All bits are 25mm long and made from S2 steel
- Magnetic bit holder and hand driver included
- Innovative storage tray allows easy access to components but guards against accidental loss by holding all pieces in place even if tray is inverted or dropped



## Professionally approved products.

Kit Contents			
Slotted Bits	Pozidriv® or Cross-recess bits	Philips® Bits	Hexagon bits (mm)
3,4,5,5,7	Pz0, Pz1, Pz2, Pz3	Ph0, Ph1, Ph2, Ph3	2, 2.5, 3, 4, 5, 6, 7