

**Professionally approved products.**

## Datasheet

# 10 inch Adjustable Spanner

RS Stock number [541-6595](#)



### Specification:

- Material: Chrome vanadium steel (CR-v steel 6150 ) for adjustable wrenches
- Finish: Phosphate black finish, polish jaw portion with laser scale with logo
- Hardness: Heat treated to HRC: 42 ~ 48

### Contents:

1 pc-10" (250mm) wide jaw adjustable wrenches with laser metric scales (overall length - 255 mm, max jaw opening - 30 mm, net weight - 440g)

### Remarks:

Torque, hardness and gauges meet din 3117 standard.