

FEATURES

- NiCd chemistry

RS PRO 10x 2/3A 10S1P 12V 0.65Ah ST2 AMP Automatic door battery

RS Stock No.: 2466436



Compatible with Manusa Bravo, Osgio and Palma

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

General Specifications

Technology	NICD
Type	2/3A
Designation	10s1p
Nominal Voltage	12v
Nominal Capacity	0.65Ah
Operating Voltage	9V to 14V
Operating Temperature	Charge 0 to 45°C Discharge -30 to 60°C
Storage Temperature	-30 to 35°C
Internal Resistance (At 1000HZ)	< 50m Ω
Shelf Life	1 Years

Mechanical Specifications

Dimensions (MM)	83.7 x 33.8 x 30.6 (+/-1)
Weight (G)	178 gr (+/-1)
Covering	Shrink Sleeve
Wire (Black+Red)	18 AWG
Length of wire (CM)	10 (+/5)
Output Connector	AMP Mate and Lock 2 PTS

Approvals

Certification	None
UN Classification	UN 2800
Battery Energy	7.8 WH
Transport Rescriptions	None