USB-A to USB-C Adapter, USB-A Male to USB-C Female Converter, USB 10Gbps, 5V 900mA, USB to USB C Adapter for USB-A Chargers/Hubs

Product ID: U32-AMCF-USBADAPTER

Connect a USB-C cable to a USB-A laptop or convert a USB-A port to Type-C using this compact USB-A Male to USB-C Female adapter. The compact, streamlined design ensures straightforward connectivity without blocking adjacent ports, and supports USB 10Gbps performance for fast data transfer.

The USB-A to USB-C adapter is universally compatible with any operating system. Simple plug-and-play setup enables instant deployment. The adapter supports USB 10Gbps and facilitates up to 5V/900mA output from a powered USB-A connection such as a wall charger. This enables consistent charging to a USB-C device from a USB-A source. Please note that USB-C video and Power Delivery are not supported.

The USB-A to USB-C adapter features a durable PVC housing that protects against everyday wear. Nickel-plated connectors ensure a flush fit to help reduce signal loss, providing reliable performance for frequent use.

Certifications, Reports and Compatibility

RoHS Compliant

Applications

• Connect a USB-C device to a USB-A laptop, hub, or charger

• Charge a USB-C device with up to 5V/1.5A from a USB-A charger or port

• Slim, compact housing is durable and will not obstruct adjacent ports

Features

• Add USB-C Connectivity to Any USB-A Host: Use this slim USB-A Male to USB-C Female adapter to connect USB-C cables and portable devices to USB-A laptops, chargers, and hubs; Note: USB-C video and PD are not supported

• Extend Legacy System Compatibility: Access USB-C devices from compatible USB-A workstations, adding full USB 10Gbps performance on systems without native USB Type-C ports; This adapter works with USB-C peripherals only and does not support USB-C docks and video adapters

• Quick Driverless Setup: Simple plug-and-play installation requires no drivers and works across all operating systems; Attach the adapter to any USB-A port and connect your USB-C cable and device to start syncing or charging, up to 5V 900mA

• Compact Form Factor: Slim, compact design prevents the obstruction of adjacent device ports and is ideal for small laptops and USB hubs; Robust PVC outer housing enhances durability and wear protection

• The IT Pro's Choice: Our USB-C adapters and cables are rigorously tested in our in-house Innovation Lab for reliable performance, durability, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware		
	Warranty	Lifetime
	Active or Passive Adapter	Passive
	Ports	1
	Connector Plating	Nickel
	Chipset ID	VL162
Performance		
	Maximum Data Transfer Rate	10Gbps
Connector(s)		
	Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
	Connector B	1 - USB Type-A (9 pin, 5 Gbps)
Power		
	Input Voltage	5V DC
	Input Current	900mA
Environmental		
	Operating Temperature	0 to 40 (32&degF to 104&degF)

	Storage Temperature	-10 to 70 (14&degF to 158&degF)
	Humidity	10%~90%
Physical Characteristics		
	Color	Black
	Connector Style	Straight
	Material	PVC
	Product Length	1.6 in [4.0 cm]
	Product Width	0.6 in [1.6 cm]
	Product Height	0.3 in [7.6 mm]
	Weight of Product	0.2 oz [5 g]
Packaging Information		
	Package Length	3.1 in [8.0 cm]
	Package Width	3.9 in [10.0 cm]
	Package Height	0.4 in [1.0 cm]
	Shipping (Package) Weight	0.4 oz [11.5 g]
What's in the Box		
	Included in Package	1 - USB-A Male to USB-C Female Adapter

Product appearance and specifications are subject to change without notice.