

Eaton M22-L-G

Catalog Number: M22-L-G

Eaton M22 modular pushbutton, Indicating Light Operator, Flush, IP66, NEMA 4X, 13, Rk resistance 4.7, Illuminated, Green, 100, 000 Hours of operation

General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-L-G

UPC

786685278551

Product Length/Depth

2 in

Product Height

1 in

Product Width

2 in

Product Weight

.1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked Bureau Veritas GoST-R

Certifications

CCC Marked CSA Certified Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.



Product specifications

Light color

Green

Series

M22

Type

Indicating Light

Operating Cycles

100,000 Hours of operation

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 4.7

Illumination

Illuminated

Size

22.5 mm

Button color

Green

Actuator

Flush

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[M22-L AutoCAD 2D Footprint \(mm\)](#)

[M22-L 3D Inventor](#)

[M22-L 2D Drawing Xchange](#)

[M22-L 2D PDF](#)

[M22-L AutoCAD 2D Footprint](#)

[M22-L 3D Model Xchange](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-L-G](#)

[Eaton Specification Sheet - M22-L-G](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)