

Eaton M22-L-Y

Catalog Number: M22-L-Y

Eaton M22 modular pushbutton, Indicating Light Operator, Flush, IP66, NEMA 4X, 13, Rk resistance 470, 22.5 mm, Yellow, Illuminated, White, 100, 000 Hours of operation

General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-L-Y
UPC	Product Length/Depth
786685278650	2 in
Product Height	Product Width
1 in	2 in
Product Weight	Warranty
.1 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
Bureau Veritas CE Marked GoST-R	CCC Marked CSA Certified Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.



Product specifications

Light color

White

Series

M22

Type

Indicating Light

Operating Cycles

100,000 Hours of operation

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 470

Illumination

Illuminated

Size

22.5 mm

Button color

Yellow

Actuator

Flush

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[M22-L 3D Model Xchange](#)

[M22-L 3D Inventor](#)

[M22-L AutoCAD 2D Footprint \(mm\)](#)

[M22-L 2D PDF](#)

[M22-L 2D Drawing Xchange](#)

[M22-L AutoCAD 2D Footprint](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-L-Y](#)

[Eaton Specification Sheet - M22-L-Y](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)