

Eaton M22-L-W

Catalog Number: M22-L-W

Eaton M22 modular pushbutton, Indicating Light Operator, Flush, IP66, NEMA 4X, 13, Rk resistance 47, Illuminated, White, 100, 000 Hours of operation

General specifications

| | |
|--|--|
| Product Name | Catalog Number |
| Eaton M22 modular pushbutton | M22-L-W |
| UPC | Product Length/Depth |
| 786685278612 | 2 in |
| Product Height | Product Width |
| 1 in | 2 in |
| Product Weight | Warranty |
| .05 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Compliances | Certifications |
| CE Marked Bureau Veritas GoST-R | CSA Certified CCC Marked Lloyd's Register Certified |
| Catalog Notes | |
| Includes contact block mounting adapter. | |



Product specifications

Light color

White

Series

M22

Type

Indicating Light

Operating Cycles

100,000 Hours of operation

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 47

Illumination

Illuminated

Size

22.5 mm

Button color

White

Actuator

Flush

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[M22-L AutoCAD 2D Footprint \(mm\)](#)

[M22-L 3D Inventor](#)

[M22-L 2D Drawing Xchange](#)

[M22-L 2D PDF](#)

[M22-L AutoCAD 2D Footprint](#)

[M22-L 3D Model Xchange](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-L-W](#)

[Eaton Specification Sheet - M22-L-W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)