

MODLINK MSDD DBL COMBI INSERT USA 2XNEMA 5-15

GFCI+2xRJ45 female/female + 1x3A fuse

2× NEMA-GFCI 5-15 (screw terminals)
 2× RJ45, 8-pole metal, CAT5e (female/female)
 1× fuse (3 A)
 with touch protection

[Link to Product](#)**Illustration**

Product may differ from Image

**General data**

Dimensions HxWxD	88×116×72 mm
------------------	--------------

RJ45

Operating current (UL Rating)	max. 175 mA
Locking of ports	Snap In
Connection front side	RJ45
Connection rear side	RJ45
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

Fuse

Operating voltage	250 V AC/32 V DC
Continuous load	3 A

USA

Operating current	15 A
Operating voltage	125 V AC
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 6 mm ² (AWG 10)

Product article number of manufacturer	4000-68000-4120000
--	--------------------