

FEATURES

- High power
- Loud sound output
- RoHS

RS PRO MULTIMEDIA SPEAKER

RS Stock No: 2368262



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.


MULTIMEDIA SPEAKER



Technical Specifications

Item	Specifications
Size	102mm*102mm*44mm
Impedance	4±15%
Resonance frequency	120±20%
Rated input power	20W
Maximum input power	30W
Buzz & Rattle	Must be normal
SPL(1W 1m sine wave)	79±3dB(at 0.5K,0.6K,0.8K,1.0KHz average)
THD(1W/1m,1000Hz)	MAX 5%
Operating temperature	-25~+70℃
Storage temperature	-25~+70℃
Weight	≈270g


Dimensional drawings




MULTIMEDIA SPEAKER



Frequency Response Curve (only for reference)




F0 Curve (only for reference)



MULTIMEDIA SPEAKER



Total Harmonic Distortion (only for reference)



R&B Curve (only for reference)

