

Eaton 12BDGHA10

Catalog Number: 12BDGHA10

Air fuse-link, medium voltage, 10 A, AC 12 kV, 359 x 50.8 mm, back-up, BS, with striker -12BDGHA10

General specifications

Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12BDGHA10
	UPC
	051712240949
EAN	Product Length/Depth
5027590431101	359 mm
Product Height	Product Width
50.8 mm	50.8 mm
Product Weight	Warranty
2100 g	Not Applicable
Compliances	
BS 2692-1	



Product specifications

Interrupt rating

40 kAIC

Element

Silver

Standard

British Standard

Release characteristic

Other

Mounting method

Clip-in

Amperage Rating

10 A

Fuse type

BDGH

Rated frequency - min

50 Hz

Fuse size

51 x 359 mm

With striker

Yes

Voltage rating

12 kV

Fuse indicator

With Striker

Rated frequency - max

50 Hz

Performance Cat According To IEC 60282-1

Back-up

Construction size

51 x 359 mm

Construction type

Bolt-on

Utilization category

Other

Barrels

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

12BDGHA10~12KV 10AMP 2 'A' AIR FUSE

Specifications and datasheets

Eaton Specification Sheet - 12BDGHA10

1

Resistance

138 ohms

Type

Fuse

Fuse diameter

51 mm

Fuse shape

Cylindrical

Breaking capacity

40 kA

Class

Class back-up

Pre arc (I₂T)

6.4 x 101

Product application

Primary side transformer protection

Application

protection of primary side transformers

used in fuse switch combination units, fuse bases and fuse switches

Installation technique

Air

Voltage type

AC