



LED AR111

12AR111/LED/927/S8/DIM/EC 12V 6/1FB

With an elegant new design, Philips MasterClass LED AR111 creates a brilliant visual effect. With excellent rendering of 90+ CRI and R9>50, colors stay vibrant and natural, enhancing the appeal of everything on display.

Product data

General information	
Base	G53 [G53]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	40000 h
Switching Cycle	50000
Light technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	8 °
Initial lumen (Nom)	650 lm
Luminous Intensity (Nom)	8000 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	54.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	- Hz
Power (Rated) (Nom)	12 W
Lamp Current (Nom)	1300 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s


Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	AR111
Approval and application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	No
Product data	
Order product name	12AR111/LED/927/S8/DIM/EC 12V 6/1FB
EAN/UPC - Product	046677552442
Order code	552448

LED AR111

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002238404

Net Weight (Piece)	0.353 lb
--------------------	----------


Dimensional drawing




12AR111/LED/927/S8/DIM/EC 12V 6/1FB

Product	D	C
12AR111/LED/927/S8/DIM/EC 12V 6/1FB	4-3/8 in	2-1/2 in


Photometric data



LEDspots 50W G53 AR111 927 8D




LEDspots 50W G53 AR111 927 8D




LEDspots 50W G53 AR111 927

LED AR111

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram

