

# Eaton BSPMA3480DLGR

Catalog Number: BSPMA3480DLGR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, 230/400 Wye (4W+G), Surge arrester, Thermoplastic, UL94V1, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series BSPM series surge arrester	BSPMA3480DLGR
	UPC
	051712709088
<b>Product Length/Depth</b>	<b>Product Height</b>
2.13 in	3.54 in
<b>Product Width</b>	<b>Product Weight</b>
2.56 in	.73 lb
<b>Warranty</b>	<b>Compliances</b>
Five year limited warranty	Contact factory RoHS Compliant
<b>Certifications</b>	
UL 94V0 UL Listed	



## Product specifications

### Special features

Technology type MOV

### Material

Thermoplastic

### Enclosure

Thermoplastic, UL94V1

### Surge current

200 kA

### Mounting Method

35 mm DIN rail

### Nominal Discharge Current

20 kA

### Short-circuit rating

200 kA

### Type

Surge arrestor

### Operating voltage

385

### Indicator type

Remote contact

### Frequency rating

50/60 Hz

### Operating temperature

-35 to 85 °C

### Voltage rating

230/400 Wye (4W+G)

### Application

Surge Protection

### Degree of protection

IP20

## Resources

### Catalogs

BSPMA3480DLGR~480V Delta, 3P

Bussmann series complete full line catalog no. 1007

### Specifications and datasheets

Eaton Specification Sheet - BSPMA3480DLGR



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)