

LED B11

3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20

Philips LED B11 candles offer energy saving ambiance with the elegant effect of incandescent candles. These designs provides light in an omnidirectional manner, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General information	
Base	E12 [Candelabra Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Tier	MasterClass

Light technical	
Color Code	927-922 [CCT of 2700K-2200K]
Initial lumen (Nom)	300 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	3.3 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.75
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	122 °F

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	B11 [B 35mm]


Approval and application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star

Product data	
Order product name	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20
EAN/UPC - Product	046677549565
Order code	549568
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

LED B11

Material Nr. (12NC)	929001969404
Net Weight (Piece)	0.035 lb



Dimensional drawing



3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20


Product	D	C
3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	1-3/8 in	3-15/16 in

Photometric data



LEDbulb E12 E26 BA11 B11 927 CL-LDD


LEDbulb 3.3W E12 B11 927 CL



LEDbulb 927 CL-POC

LED B11

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

