



# TrueForce High Lumen PAR

## 33PAR38/PER/830/S15/DIM/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data


General information		Lamp Current (Nom)	
Base	E26 [ Single Contact Medium Screw]		300 mA
EU RoHS compliant	Yes	Wattage Equivalent	250 W
Nominal Lifetime (Nom)	25000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000	Warm Up Time to 60% Light (Nom)	0.5 s
Tier	MasterClass	Power Factor (Nom)	0.95
		Voltage (Nom)	120 V
Light technical		Temperature	
Color Code	830 [ CCT of 3000K]	T-Case Maximum (Nom)	194 °F
Beam Angle (Nom)	15°		
Initial lumen (Nom)	3000 lm	Controls and dimming	
Luminous Intensity (Nom)	35000 cd	Dimmable	Yes
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K	Mechanical and housing	
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Finish	Clear
Color Consistency	<4	Bulb Material	Aluminum
Color Rendering Index (Nom)	80	Bulb Shape	PAR38 [ PAR 4.75 inch/121mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and electrical		Approval and application	
Input Frequency	50 to 60 Hz	Suitable For Accent Lighting	Yes
Power (Rated) (Nom)	33 W	Energy Consumption kWh/1000 h	- kWh

# TrueForce High Lumen PAR

Energy Certifications	Energy Star
<b>Product data</b>	
Order product name	33PAR38/PER/830/S15/DIM/120V 6/1FB
EAN/UPC - Product	046677534608
Order code	534602

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001916804
Net Weight (Piece)	0.937 lb


## Dimensional drawing




33PAR38/PER/830/S15/DIM/120V 6/1FB

Product	D	C
33PAR38/PER/830/S15/DIM/120V 6/1FB	4-7/8 in	5-1/4 in


## Photometric data



LEDSpot 33W E26 PAR38 S15




LEDSpot 33W E26 PAR38




LEDSpot 33W E26 PAR38 S15

# TrueForce High Lumen PAR

## Lifetime



LEDSpot 33W E26 PAR38



LEDSpot 33W E26 PAR38

