



LED R20

5R20/PER/927/P/E26/DIM 6/1FB T20

Philips R20 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Product data

General information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000
Light technical	
Color Code	927
Beam Angle (Nom)	110 °
Initial lumen (Nom)	450 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	5 W
Lamp Current (Nom)	65 mA
Wattage Equivalent	45 W
Starting Time (Nom)	0.5 s


Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	R20 [R 63mm]
Approval and application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
Product data	
Order product name	5R20/PER/927/P/E26/DIM 6/1FB T20
EAN/UPC - Product	046677553883
Order code	553883

LED R20

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002092204

Net Weight (Piece)	0.077 lb
--------------------	----------


Dimensional drawing




5R20/PER/927/P/E26/DIM 6/1FB T20

Product	D	C
5R20/PER/927/P/E26/DIM 6/1FB T20	2-9/16 in	3-15/16 in


Photometric data



LEDbulb 45W E26 R20 927 Frosted



LEDbulb 45W E26 R20 927 Frosted





© 2022 Philips Lighting B.V. Page 11

LEDbulb 45W E26 R20 927 Frosted

LED R20

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

