



LED Corn Cobs

63CC/LED/830/LS EX39 G3 BB 3/1

Philips Corn Cob HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data


General information	
Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000
Tier	CorePro
Light technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	8600 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	136.00 lm/W
Color Consistency	ANSI 4000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	63 W
Lamp Current (Nom)	700 mA
Wattage Equivalent	250(175-250) W
Starting Time (Nom)	1 s

Warm Up Time to 60% Light (Nom)	1 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	100-277 V
Temperature	
T-Ambient (Max)	113 °F
T-Ambient (Min)	-4 °F
T-Case Maximum (Nom)	149 °F
Controls and dimming	
Dimmable	Preset Dimming
Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Corncob
Product data	
Order product name	63CC/LED/830/LS EX39 G3 BB 3/1
EAN/UPC - Product	046677564230
Order code	564237
Numerator - Quantity Per Pack	1

LED Corn Cobs

Numerator - Packs per outer box	3
Material Nr. (12NC)	929002999804
Net Weight (Piece)	1.799 lb



Dimensional drawing



63CC/LED/830/LS EX39 G3 BB 3/1


Product	D	C
63CC/LED/830/LS EX39 G3 BB 3/1	3-3/8 in	10-1/4 in

Photometric data



LEDForce LS EX39 63W Corncob EX39-LDD


LEDForce LS EX39 63W Corncob EX39 830-GUL



LEDForce LS EX39 36W Corncob EX39 830-POC

LED Corn Cobs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

