



A-Shape LED

16A19/PER/940/P/E26/DIM 6/1FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General information		Warm Up Time to 60% Light (Nom)	
Base	E26 [Single Contact Medium Screw]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.7
Nominal Lifetime (Nom)	15000 h	Voltage (Nom)	120 V
Switching Cycle	50000	Temperature	
Tier	CorePro	T-Case Maximum (Nom)	194 °F
Light technical		Controls and dimming	
Color Code	940 [CCT of 4000K]	Dimmable	Yes
Beam Angle (Nom)	250 °	Mechanical and housing	
Initial lumen (Nom)	1600 lm	Bulb Finish	Frosted
Color Designation	Cool White (CW)	Bulb Material	Plastic
Correlated Color Temperature (Nom)	4000 K	Bulb Shape	A19 (A19)
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Approval and application	
Color Consistency	<4	Energy Consumption kWh/1000 h	- kWh
Color Rendering Index (Nom)	90	Energy Certifications	Energy Star
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product data	
Operating and electrical		Order product name	16A19/PER/940/P/E26/DIM 6/1FB T20
Input Frequency	60 Hz	EAN/UPC - Product	046677561451
Power (Rated) (Nom)	16 W	Order code	561456
Lamp Current (Nom)	135 mA	Numerator - Quantity Per Pack	1
Wattage Equivalent	100 W		
Starting Time (Nom)	0.5 s		

A-Shape LED

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

