



LED AR111

20AR111/LED/930/F15 DIM 12V 6/1FB

With an elegant new design, Philips MasterClass LED AR111 creates a brilliant visual effect. With excellent rendering of 90+ CRI and R9>50, colors stay vibrant and natural, enhancing the appeal of everything on display.

Product data

General information	
Base	G53 [G53]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000
Light technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	15 °
Initial lumen (Nom)	1200 lm
Luminous Intensity (Nom)	8000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	91
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	- Hz
Power (Rated) (Nom)	20 W
Lamp Current (Nom)	2400 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s


Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	176 °F
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	AR111
Approval and application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	No
Product data	
Order product name	20AR111/LED/930/F15 DIM 12V 6/1FB
EAN/UPC - Product	046677552374
Order code	552372

LED AR111

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002239604

Net Weight (Piece)	0.353 lb
--------------------	----------


Dimensional drawing



20AR111/LED/930/F15 DIM 12V 6/1FB


Product	D	C
20AR111/LED/930/F15 DIM 12V 6/1FB	4-3/8 in	2-1/2 in

Photometric data




Technical Document 11 Page Lighting 11 Page 111

LEDspots 20W AR111 G53 930 15D



LEDspots 20W AR111 G53 930 15D



LEDspots 20W AR111 G53 930 15D

LED AR111

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram

