



LED B11

3.3B11/PER/950/CL/G/E12/DIM 1FBT20

Philips LED B11 candles offer energy saving ambiance with the elegant effect of incandescent candles. These designs provides light in an omnidirectional manner, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General information	
Base	E12 [Candelabra Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	3.3-40W

Light technical	
Color Code	950 [CCT of 5000K]
Initial lumen (Nom)	300 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	3.3 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	122 °F

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	B11 [B 35mm]

Approval and application	
Energy Consumption kWh/1000 h	- kWh


Product data	
Order product name	3.3B11/PER/950/CL/G/E12/DIM 1FBT20
EAN/UPC - Product	046677549145
Order code	549147
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002205904

LED B11

Copy Net Weight (Piece)

0.035 lb



Dimensional drawing



3.3B11/PER/950/CL/G/E12/DIM 1FBT20

Product	D	C
3.3B11/PER/950/CL/G/E12/DIM 1FBT20	1-3/8 in	3-15/16 in


Photometric data



Copyright © 2012, All rights reserved. Page 17

LEDbulb E12 E26 BA11 B11 927 CL-LDD

LEDCandle 40W E12 B11 950 CL



LEDbulb 40,60W E26 950

LED B11

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

