

Type ANX-I Automotive Blade Fuse Maxi Size – LED Indicating



www.optifuse.com (619) 593-5050


Specifications:

- Voltage: 32VDC
- Amperage: 20A, 30A, 40A, 50A, 60A, 70A, 80A, 100A
- Body: PA 66
- Indicating LED when fuse is opened
- Terminals: Zinc alloy
- Designed to meet SAE and ISO 8820 Standards.
- Interrupt Rating – 1000A @ 32 VDC


Part Number	Amperage	Body Color
ANX-I-20A	20A	Yellow
ANX-I-30A	30A	Green
ANX-I-40A	40A	Orange
ANX-I-50A	50A	Red
ANX-I-60A	60A	Blue
ANX-I-70A	70A	Tan
ANX-I-80A	80A	Clear
ANX-I-100A	100A	Violet

Time Characteristics:			
% of Rated Current	Current Rating	Min Hold Time	Max Hold Time
135%	20~60A	60s	1800s
135%	70~100A	60s	3600s
200%	20~100A	4s	60s
350%	20~100A	200ms	7s

Mechanical Dimensions: Inches [mm]



Time Characteristics



	Warning: -Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.
	-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.