



9716SW8808

## INDOOR REPLACEMENT ROUND POWER SUPPLY CORDS

- Temperature Rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Vacuum, Electric Drill, Work Light

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
9702SW8808	16/2	SJTW	6'	1.8 m	Black	13	25
9703SW8808	16/3	SJTW	3'	0.9 m	Black	13	25
9706SW8808	16/3	SJTW	6'	1.8 m	Black	13	25
9709SW8808	16/3	SJTW	9'	2.7 m	Black	13	25
9716SW8808	14/3	SJTW	6'	1.8 m	Black	15	25
9719SW8808	14/3	SJTW	9'	2.7 m	Black	15	25



9734SW8809

## INDOOR REPLACEMENT FLAT POWER SUPPLY CORDS

- Temperature Rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Microwave, Refrigerator, Dehumidifier

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
9723SW8809	16/3	SPT-3	3'	0.9 m	Gray	13	25
9733SW8809	16/3	SPT-3 Straight	3'	0.9 m	Gray	13	25
9724SW8809	16/3	SPT-3 R/Angle	4'	1.2 m	Gray	13	25
9734SW8809	16/3	SPT-3 Straight	4'	1.2 m	Gray	13	25
9726SW8809	16/3	SPT-3 R/Angle	6'	1.8 m	Gray	13	25
9736SW8809	16/3	SPT-3 Straight	6'	1.8 m	Gray	13	25
9743SW8823	14/3	SPT-3 Straight	3'	0.9 m	Beige	15	25
9743SW09	14/3	SPT-3 Straight	3'	0.9 m	Gray	15	25
9746SW8823	14/3	SPT-3 Straight	6'	1.8 m	Beige	15	25
98700009	12/3	SPT-3	6'	1.8 m	Beige	15	25



3533SW3323

## INDOOR MAJOR APPLIANCE REPLACEMENT CORDS

- Temperature Rating of -4°F to 140°F (-20°C to 60°C)
- 125 Voltage Rating (250 Voltage Rating for 3537SW8809)
- Common Applications: Air Conditioner, Space Heater, Refrigerator

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
3531SW3323	14/3	SPT-3	3'	0.9 m	Beige	15	36
3531SW09	14/3	SPT-3	3'	0.9 m	Gray	15	24
3532SW3323	14/3	SPT-3	6'	1.8 m	Beige	15	24
3532SW09	14/3	SPT-3	6'	1.8 m	Gray	15	24
3533SW3323	14/3	SPT-3	9'	2.7 m	Beige	15	18
3535SW3323	14/3	SPT-3	12'	3.7 m	Beige	15	12
3536SW3323	14/3	SPT-3	15'	4.6 m	Beige	15	12
3537SW8809*	12/3	SPT-3	9'	2.7 m	Gray	20	18

\*6-20 P/R