



- 2 x  $\phi$  3.30 [0.130] THRU ALL
- M4 - 6H THRU ALL
- ✓  $\phi$  4.05 [0.159] X 90°, Near Side
- ✓  $\phi$  4.05 [0.159] X 90°, Far Side