

ROYAL[®] WELDING CORDS



Royal[®] extension cords are resistant to welding slag and are the most flexible extension cord on the market.

- Temperature Rating of -40°F to 194°F (-40°C to 90°C)
- 125 Voltage Rating
- Abrasion, chemical, and oil resistant
- Common Applications: Welder, Angle Grinder, Rotary Hammer Drill

SPECIFICATIONS

OUTDOOR EXTENSION CORDS W/ POWER LIGHT INDICATOR



3678SW0008

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
3677SW0008	12/3	SJ00W	25'	7.6 m	Black	15	12
3687SW0002	12/3	SJ00W	25'	7.6 m	Yellow	15	12
3678SW0008	12/3	SJ00W	50'	15.2 m	Black	15	6
3688SW0002	12/3	SJ00W	50'	15.2 m	Yellow	15	6
3679SW0008	12/3	SJ00W	100'	30.5 m	Black	15	4
3689SW0002	12/3	SJ00W	100'	30.5 m	Yellow	15	4