


APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	
A		ADDED P/N OPTIONS	10/1/18	HR/RC1
B		ADDED 1M LENGTH	2/15/22	LH/KL



P1		P2
1	BROWN	1
3	WHITE	3
2	RED	2
4	WHITE	4
6		6
5	ORANGE	5
7	WHITE	7
9		9
8	GREEN	8
10	WHITE	10
12		12
11		11
19	BLUE	19
14	WHITE	14
17		17
13	WHITE	13
15	YELLOW	15
16	ORANGE	16
18	RED	18
S	BRAID&DRAIN	S

ADAM P/N	L
CA-HDMI-AM/AM-3FT	36.024"±1.181" [915±30mm]
CA-HDMI-AM/AM-3.3FT	39.370"±1.181" [1000±30mm]
CA-HDMI-AM/AM-6FT	72.047"±1.969" [1830±50mm]
CA-HDMI-AM/AM-10FT	120.079"±1.969" [3050±50mm]
CA-HDMI-AM/AM-16.5FT	198.425"±1.969" [5040±50mm]

SPECIFICATIONS:

Connector:

P1=P2= HDMI A Type Plug, Overmold Color: Black, 50P PVC

Cable:

U20276, [(30#*1P+D+A+M)*5C+30#*4C]+A+D+B<64#>, (HDMI 1.4 Cable)

O.D: .236" [6mm], Jacket Color: Black

Electrical Test:

All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	±.10	Ø.X	±.10
.XX	±.020	Ø.XX	±.015
.XXX	±.015	Ø.XXX	±.010

DRAWN	HR	10/13/15
CHECKED	TW	10/13/15
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH



909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	CUSTOM ASSEMBLY, UL20276, HDMI A TYPE PLUG TO HDMI A TYPE PLUG	
SIZE	PART NO.	REV.
X	CA-HDMI-AM/AM-XFT	B

REF:	S00087T	SCALE:	NTS	SHEET	1 OF 1
------	---------	--------	-----	-------	--------