





Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/04	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATION:

Material:
Insulator: PBT, rated UL-94V-0
Contacts: Brass
Contact Plating:
Gold Flash over Nickel underplate overall
Electrical:
Operating Voltage: 250V AC max.
Current rating: 3 Amps max.
Contact resistance: 20 mohms max
Insulation resistance: 5000 Mohms min
Dielectric withstanding voltage: 1000 VAC / minute
Mechanical:
Mating durability: 500 cycles min.
Temperature Rating:
Operating temperature: -55° TO +105°
Environmental:
Lead free, RoHS compliant.



A = .100 [2.54] X No. of Positions / 2 + .300 [7.60]
B = .100 [2.54] X No. of Positions / 2 + .200 [5.08]
C = .100 [2.54] X No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
INCHES HOLES					
.X ± .10	∅X ± .10		TITLE BOX HEADER, VERTICAL PCB MOUNT, 2 ROW .100 PITCH, GOLD FLASH PLATED		
.XX ± .020	∅XX ± .015				
.XXX ± .015	∅XXX ± .010		SIZE X	PART NO. BHR-XX-VUA	REV. -
APPROVALS			REF:	SCALE: NTS	SHEET 1 OF 1
DRAWN	SS	DATE			
CHECKED		11/16/04			
APPROVED					