




Mechanical Dimensions: Inches [mm]



Mounting Hole



Circuit Diagram



Electrical Specifications

Continuous Rating	200A 32V DC
Intermittent Rating	300A
Cranking Rating	1000A for 5secs
Insulation Resistance	DC 500V 1M ohm Min.
Operation Temperature	-30°C ~ 60°C

Material Specifications

Material Specifications		
	IP56	
Housing	Nylon with 33% Fiberglass	
Bottom	PBT with 15% Fiberglass	
Terminals / Contacts	Brass, Nickel plated	
Actuator	PBT with 15% Fiberglass	

Battery Switch

BC3-DC



Rev	Date of issue	Revision Notes	Designed	Approved
Α	12-14-2020	Initial Drawing	RC	OF