

CUSTOMER PRINT


PART NUMBER: CARA6C806SPXXX90

NOTES:

1. FINISHED PRODUCT TO BE COILED
2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
3. ELECTRICAL TEST: 100% CONTINUITY
4. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	"X" DIM
CARA6C806SP03990	3 FT. 3 1/2 IN. ±2 IN. [1M ±50.8mm]
CARA6C806SP07990	6 FT. 7 IN. ±2 IN. [2M ±50.8mm]
CARA6C806SP19790	16 FT. 5 IN. ±4 IN. [5M ±101.6mm]
CARA6C806SP39490	32 FT. 9 3/4 IN. ±8 IN. [10M ±203.2mm]
CARA6C806SPXXX90	

CABLE CUT LENGTH IN "INCHES"



END "A" FACE VIEW

DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS UNLESS INDICATED

WIRE COLOR CODE

POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6
BLK	WHT	RED	BLU	GRN	YEL
16 AWG	16 AWG	20 AWG	20 AWG	20 AWG	20 AWG

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

A	MA	08-19-21	DRAWING CREATED PER DOR 21-109361DS-1		
REV.	INIT.	DATE	DESCRIPTION		
	MA	08-19-21	ORIG. DRAWN BY: _____ DATE: 08-19-21 CHECKED BY: _____ APPROVED BY: _____ TITLE: CABLE ASSEMBLY, RA 2#16/4#20 SOCKET CONTACTS INSTA-CLICK™ MINI-CON-X MIX SIG BULLET CUSTOMER: STANDARD PRODUCT		
SCALE		SIZE	SHEET		FILE: CARA6C806SPXXX90 DIRECTORY: SLW PART NUMBER: CARA6C806SPXXX90 REV A
NTS		B	1 OF 1		



CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX