

CUSTOMER PRINT


PART NUMBER: CARA6A808SPXXX90

NOTES:

1. FINISHED PRODUCT TO BE COILED
2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
3. ELECTRICAL TEST: 100% CONTINUITY
4. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	"X" DIM
CARA6A808SP03990	3 FT. 3 1/2 IN. ±2 IN. [1M ±50.8mm]
CARA6A808SP07990	6 FT. 7 IN. ±2 IN. [2M ±50.8mm]
CARA6A808SP19790	16 FT. 5 IN. ±4 IN. [5M ±101.6mm]
CARA6A808SP39490	32 FT. 9 3/4 IN. ±8 IN. [10M ±203.2mm]
CARA6A808SPXXX90	

CABLE CUT LENGTH IN "INCHES"



WIRE COLOR CODE							
POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6	POS. 7	POS. 8
BLK	WHT	BRN	RED	YEL	GRN	GRY	BLU
16 AWG	16 AWG	26 AWG	26 AWG	26 AWG	26 AWG	26 AWG	26 AWG

DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS UNLESS INDICATED

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_  
DATE: \_\_\_\_\_

**RoHS COMPLIANT**

A	MA	08-13-21	DRAWING CREATED PER DOR 21-109361DS-1
REV.	INIT.	DATE	DESCRIPTION
	MA	08-13-21	ORIG. DRAWN BY: MA DATE: 08-13-21
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			 601 E. WILDWOOD VILLA PARK, IL 60181
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			
APPROVED BY:		TITLE: CABLE ASSEMBLY, RA 2#16/6#26 SOCKET CONTACTS INSTA-CLICK™ MINI-CON-X MIX SIG BULLET CUSTOMER: STANDARD PRODUCT	
SCALE	SIZE	SHEET	PART NUMBER: CARA6A808SPXXX90
NTS	B	1 OF 1	REV A
FILE:	DIRECTORY:	PART NUMBER:	
CARA6A808SPXXX90	SLW	CARA6A808SPXXX90	