

CUSTOMER PRINT


PART NUMBER: CARA6C806SXXX90

NOTES:

1. FINISHED PRODUCT TO BE COILED
2. OVERMOLD BOOT MATERIAL: PVC, BLACK
3. ELECTRICAL TEST: 100% CONTINUITY
4. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	"X" DIM
CARA6C806S03990	3 FT. 3 1/2 IN. ±2 IN. [1M ±50.8mm]
CARA6C806S07990	6 FT. 7 IN. ±2 IN. [2M ±50.8mm]
CARA6C806S19790	16 FT. 5 IN. ±4 IN. [5M ±101.6mm]
CARA6C806S39490	32 FT. 9 3/4 IN. ±8 IN. [10M ±203.2mm]
CARA6C806SXXX90	

CABLE LENGTH IN "INCHES"



WIRE COLOR CODE					
POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6
BLK	WHT	RED	BLU	GRN	YEL
16 AWG	16 AWG	20 AWG	20 AWG	20 AWG	20 AWG

DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS UNLESS INDICATED

**CUSTOMER APPROVAL**

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_  
DATE: \_\_\_\_\_

A	MA	07-29-21	DRAWING CREATED PER DOR 21-109361DS		
REV.	INIT.	DATE	DESCRIPTION		
	MA	07-29-21	ORIG. DRAWN BY: DATE: MA 07-29-21		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			<p>601 E. WILDWOOD VILLA PARK, IL 60181</p>		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			TITLE: CABLE ASSEMBLY, RA 2#16/4#20 SOCKET CONTACTS MINI-CON-X MIXED SIGNAL FLEX OM STANDARD PRODUCT		
APPROVED BY:		SCALE: NTS		SIZE: B	SHEET: 1 OF 1
FILE: CARA6C806SXXX90		DIRECTORY: SLW		PART NUMBER: CARA6C806SXXX90	
					REV A

**RoHS COMPLIANT**

CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX