

PVC Cable Guard for rewirable connectors



black
square
Press-Fit Version

See below:

[Approvals and Compliances](#)

Description

- Press-Fit Version
- bend protection for cable

Weblinks

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Approvals](#), [Distributor-Stock-Check](#), [Accessories](#), [Detailed request for product](#)

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
	Designed for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements

Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

All Variants

Suitable for	Color	For cables with outer diameter of	Length [mm]	Order Number
1651, 4013, 4020, 4021, 8111, 9013	white	8.7 mm	39.4 mm	4311.0053
0104, 0104U, 0106	white	10 mm	39 mm	4311.0063
0104, 0104U, 0106	white	8 mm	38 mm	4311.0064
1651, 4013, 4020, 4021, 8111, 9013	white	10 mm	39 mm	4311.0068
0104, 0104U, 0106	black	8 - 10 mm	40.3 mm	4311.9301
0104, 0104U, 0106	grey	8 - 10 mm	40.3 mm	4311.9302
1651, 4013, 4020, 4021, 8111, 9013	black	8.5 - 10 mm	40.3 mm	4311.9305
1651, 4013, 4020, 4021, 8111, 9013	grey	8.5 - 10 mm	40.3 mm	4311.9306
1251	black	6.5 mm	30 mm	4311.9309
0101, 0102, 0104, 0104U, 0106, 0112	black	8 mm	38 mm	4311.9310
0101, 0102, 0112	black	10 mm	40 mm	4311.9313

Suitable for	Color	For cables with outer diameter of	Length [mm]	Order Number
0104, 0104U, 0106	grey	10 mm	39 mm	4311.9315
1651, 4013, 4020, 4021, 8111, 9013	black	10 mm	39 mm	4311.9318
1651, 4013, 4020, 4021, 8111, 9013	grey	10 mm	39 mm	4311.9319
1251	white	6.5 mm	30 mm	4311.9324

Most Popular.

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs