




FEMALE END VIEW



SPECIFICATIONS

CONTACT CARRIER MATERIAL/COLOR	NYLON/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	30 V
CABLE OUTLET	ø6.0 to ø8.0 [0.236-0.315]
TERMINATION TYPE	SCREW
WIRE SIZE	26-20 AWG
TEMPERATURE RANGE	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	MEETS IEC IP67



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<b>TURCK INC</b> High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com			
1.							
2.			DRFT	NF	DATE	02/16/15	DESCRIPTION
3.			APVD	L.S.	SCALE	1=5	
4.		UNIT OF MEASUREMENT		MILLIMETER [ INCH ]		IDENTIFICATION NO.	REV
MATERIAL		SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		U2-24420	
FINISH		SEE SPECIFICATIONS		DO NOT SCALE THIS DRAWING		FILE: U2-24420	SHEET 1 OF 1

B	UPDATE DESCRIPTION	RDS	04/14/15	49529
REV	DESCRIPTION	BY	DATE	ECO NO.