



MALE END VIEW



DeviceNet™

SPECIFICATIONS

| | |
|-------------------------------|--|
| CONTACT CARRIER MATERIAL | NYLON OR TPU |
| MOLDED HEAD MATERIAL/COLOR | TPU/BLUE-GRAY |
| CONTACT MATERIAL/PLATING | BRASS/GOLD |
| COUPLING NUT MATERIAL/PLATING | BRASS/NICKEL |
| RATED VOLTAGE [V] | 10-30 VDC (7.6 VDC MAX. ON PINS WITH RESISTOR) |
| INTERNAL RESISTOR | 120 Ω (1/2 W) |
| PROTECTION CLASS | NEMA 1,3,4,6 AND IEC IP68, IP69K |



SOURCE DRAWING - FOR REFERENCE ONLY

| | | | | | | | |
|-------------------|--|----------------------|---|---|--------------|--|----------|
| RELATED DOCUMENTS | | 3RD ANGLE PROJECTION | | THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. | | TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com | |
| 1. | | | ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY | DRFT | CBM | DATE | 06/23/00 |
| 2. | | | | DSGN | | SCALE | 1=1.0 |
| 3. | | | | UNIT OF MEASUREMENT | | IDENTIFICATION NO. | |
| 4. | | | CONTACT TURCK FOR MORE INFORMATION | MILLIMETER [INCH] | | R2251-1 | |
| MATERIAL | | | | DO NOT SCALE THIS DRAWING | | REV | |
| FINISH | | | | FILE: U2251-1 | | G | |
| G | DRAWING PROCESSED AS PART OF ECO 33971 | CBM | 04/07/11 | 33971 | SHEET 1 OF 1 | | |
| REV | DESCRIPTION | BY | DATE | ECO NO. | | | |