


Coaxial Cable Connector 21_MCX-50-1-11/111_N

Description

Straight cable jack

Interface standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0015 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00007462
Catalogue drawing	DOU-00006340
Assembly instruction	DOC-0000182201

Ordering Information

Single package	21_MCX-50-1-11/111_NE
----------------	-----------------------

Additional Information

Suitable cables	RG_178_B/U, ENVIROFLEX_178, RG_196_A/U
-----------------	--