

## Coaxial Panel Connector 22\_MCX-50-0-2/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	6 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0008 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00010854
Catalogue drawing	DCA-00010691
Mounting hole	DOU-00008855

### Ordering Information

Bulk 100 pcs package	22_MCX-50-0-2/133_NH
----------------------	----------------------