

Coaxial Cable Connector 21_MCX-50-2-12/111_N

Description

Straight cable jack

Interface standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0013 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPRO Plating

Related Documents

Outline drawing	DOU-00006338
Catalogue drawing	DOU-00006340
Assembly instruction	DOC-0000179868

Ordering Information

Single package	21_MCX-50-2-12/111_NE
----------------	-----------------------

Additional Information

Suitable cables	K_02252_D, G_02232_D, ENVIROFLEX_316_D
-----------------	--