

## Between Series Adaptor 31\_BNC-N-75-1/133\_U

### Description

Adaptor jack/jack  
BNC jack (female) / N jack (female)

Interface standards  
Series BNC - Compatible with IEC 61169-8\_MIL-STD-348A/301\_CECC 22120  
Series N - Not compatible to N 50 Ohms



### Technical Data

#### Electrical Data

Impedance 75 Ω  
Interface frequency max. 1 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0283 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

#### Material Data

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing DCA-00014628

### Ordering Information

Single package 31\_BNC-N-75-1/133\_U