

Between Series Adaptor 33_UHF-BNC-0-1/032_-

Description

Adaptor plug/jack
UHF plug (male) / BNC jack (female)

Interface standards
Series UHF - IEC 60169-12
Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 0.2 GHz

Mechanical Data

Number of matings 500
Weight 0.0228 kg

Environmental Data

Operating temperature -25 °C to 100 °C
2011/65/EU (RoHS - including compliant
2015/863 and 2017/2102)

Material Data

Interface - UHF plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PP (Polypropylene)	
Coupling nut	Brass	Nickel Plating

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00014025

Ordering Information

Single package 33_UHF-BNC-0-1/032_-E