

Between Series Adaptor 32_BNC-N-75-1/133_U

Description

Adaptor plug/plug
BNC plug (male) / N plug (male)



Interface standards
Series BNC - Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120
Series N - Not compatible to N 50 Ohms

Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 1 GHz

Mechanical Data

Number of matings 500
Weight 0.0401 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including compliant
2015/863 and 2017/2102)

Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - N plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing DCA-00014542

Ordering Information

Single package 32_BNC-N-75-1/133_UE