

## Coaxial Cable Connector

11\_N-50-8-10/003\_-

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz
Frequency range	DC to 2.5 GHz
Return loss	30 dB

#### Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.1043 kg

#### Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver / SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

### Related Documents

Outline drawing	DOU-00007598
Catalogue drawing	DOU-00007600
Assembly instruction	DOC-0000180713

### Ordering Information

Single package	11_N-50-8-10/003_-E
----------------	---------------------

### Additional Information