

Coaxial PCB Connector 82_MCX-75-0-4/111_N

Description

Straight PCB jack

Interface Standards
SUHNER-MCX75



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0006 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | Gold Plating (Nickel underplated) |
| Body | Brass | Gold Plating (Nickel underplated) |
| Insulator | PFA / PTFE | |

Related Documents

Outline drawing DOU-00013381
Catalogue drawing DCA-00013383

Ordering Information

Bulk 100 pcs package 82_MCX-75-0-4/111_NH
Single package 82_MCX-75-0-4/111_NE

Remarks

PCB connector without stand-offs