

Coaxial Panel Connector 22_SMA-50-0-53/199_N

Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Number of matings	500
Weight	0.0019 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Fastening nut	Stainless Steel	
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DCA-00010437
Mounting hole	DOU-00010146

Ordering Information

Single package	22_SMA-50-0-53/199_NE
----------------	-----------------------