

Between Series Adaptor 31_BNC-SMA-50-1/1--_U

Description

Adaptor jack/jack
BNC jack (female) / SMA jack (female)

Interface standards
Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120
Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
VSWR	DC - 4 GHz ≤ 1.06 + 0.04 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0071 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014633
-------------------	--------------

Ordering Information

Single package	31_BNC-SMA-50-1/1--_UE
----------------	------------------------