

Han 16B-AK with stainless-steel cord




Image is for illustration purposes only. Please refer to product description.

Part number	09 30 016 5417
Specification	Han 16B-AK with stainless-steel cord
HARTING eCatalogue	https://b2b.harting.com/09300165417

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings Thermoplastic With fixing cord

Version

Size	16 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	22 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140162457
eCl@ss	27440208 Cap for industrial connectors