



ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSSS-300-B	BODY	304 STAINLESS	1
2	SRB-304 THRU SRB-316	BUSHING	NEOPRENE	1
3	RSSS-300-N	NUT	304 STAINLESS	1
4	SW-300-SS	WASHER	304 STAINLESS	1
5	SOR-3	O-RING	BUNA-N	1
6	LN-100	LOCKNUT	ADD: L, ZINC PLATED STEEL	1
7	LNSS-100	LOCKNUT	ADD: LNSS, STAINLESS STEEL	

CATALOG NUMBER	SEALING RANGE	BODY BORE
RSSS-304	.188 - .250	.990
RSSS-305	.250 - .312	.990
RSSS-306	.312 - .375	.990
RSSS-307	.375 - .437	.990
RSSS-308	.438 - .500	.990
RSSS-309	.500 - .562	.990
RSSS-310	.500 - .625	.990
RSSS-311	.562 - .688	.990
RSSS-312	.625 - .750	.990
RSSS-313	.688 - .812	.990
RSSS-314	.750 - .875	.990
RSSS-315	.812 - .938	.990
RSSS-316	.875 - 1.000	.990

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	REMKE REMKE INDUSTRIES 310 CHADDICK DR, WHEELING, IL. 60090	
A	5/13/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1° BEND ± 1° ONE PLACE DECIMAL ± .015 TWO PLACE DECIMAL ± .010 THREE PLACE DECIMAL ± .005 INTERPRET GEOMETRIC TOLERANCING PER: MATERIAL STAINLESS FINISH DO NOT SCALE DRAWING	DRAWN JCN CHECKED ENG APPR. MFG APPR. Q.A. PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.	5/13	TITLE: RSSS- 300 SERIES SIZE A DWG. NO. RSSS-300 ASSEMBLY SCALE: 1:1 SHEET 1 OF 1	

5

4

3

2

1