



ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSR-300-B	BODY	ALUMINUM	1
2	SRB-315 - SRB-316	BUSHING	NEOPRENE	1
3	RSR-300-ND	NUT	ALUMINUM	1
4	R-316-D	MESH	STAINLESS WIRE	1
5	LN-100	LOCK NUT	ADD: L, C.R.S. ZINC PLATED	1

CATALOG NUMBER	SEALING RANGE	BODY BORE
RSR-315-E	.812 - .938	.990
RSR-316-E	.875 - 1.000	.990

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	REMKE REMKE INDUSTRIES 310 CHADDICK DR, WHEELING, IL. 60090	
A	7/1/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL $\pm 1/64$ ANGULAR: MACH $\pm 1^\circ$ BEND $\pm 1^\circ$ ONE PLACE DECIMAL $\pm .015$ TWO PLACE DECIMAL $\pm .010$ THREE PLACE DECIMAL $\pm .005$	DRAWN	JCN	7/13	TITLE: RSR-315-316-E SERIES
			INTERPRET GEOMETRIC TOLERANCING PER:	CHECKED			SIZE A DWG. NO. RSR-315-316-E ASSEMBLY
			MATERIAL ALUMINUM	ENG APPR.			
			FINISH	MFG APPR.			SCALE: 2:3 SHEET 1 OF 1
			DO NOT SCALE DRAWING	Q.A.			

5

4

3

2

1