



ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSSS-200-B	BODY	304 STAINLESS	1
2	RSSS-200-N	NUT	304 STAINLESS	1
3	SRB-203 THRU SRB-213	BUSHING	NEOPRENE	1
4	SW-200-SS	WASHER	304 STAINLESS	1
5	SOR-2	O-RING	BUNA-N	1
6	LN-75	LOCKNUT	ADD: L, C.R.S. ZINC PLATED	1
7	LNSS-75	LOCKNUT	ADD: LNSS, STAINLESS STEEL	1

CATALOG NUMBER	SEALING RANGE	BODY BORE
RSSS-203	.125 - .188	.812
RSSS-204	.188 - .250	.812
RSSS-205	.250 - .312	.812
RSSS-206	.312 - .375	.812
RSSS-207	.375 - .437	.812
RSSS-208	.438 - .500	.812
RSSS-209	.500 - .562	.812
RSSS-210	.500 - .625	.812
RSSS-211	.562 - .688	.812
RSSS-212	.625 - .750	.812
RSSS-213	.688 - .812	.812

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	REMKE REMKE INDUSTRIES 310 CHADDICK DR, WHEELING, IL. 60090		
A	5/13/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1° BEND ± 1° ONE PLACE DECIMAL ± .015 TWO PLACE DECIMAL ± .010 THREE PLACE DECIMAL ± .005 INTERPRET GEOMETRIC TOLERANCING PER: MATERIAL STAINLESS FINISH DO NOT SCALE DRAWING	DRAWN JCN CHECKED ENG APPR. MFG APPR. Q.A. PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.	5/13	TITLE: RSSS-200 SERIES	SIZE A	DWG. NO. RSSS-200 ASSEMBLY
						SCALE: 1.3:1	SHEET 1 OF 1	

5

4

3

2

1