



ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSSS-300-B	BODY	304 STAINLESS	1
2	SRB-313 - SRB-314	BUSHING	NEOPRENE	1
3	SOR-3	O-RING	BUNA-N	1
4	RSSS-300-ND	NUT	304 STAINLESS	1
5	LN-100	LOCK NUT	ADD: L, C.R.S. ZINC PLATED	1
6	R-314-DSS			1



CATALOG NUMBER	SEALING RANGE	BODY BORE
RSSS-313-E	.688 - .812	.990
RSSS-314-E	.750 - .875	.990

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	<b>REMKE</b> <b>REMKE INDUSTRIES</b> 310 CHADDICK DR, WHEELING, IL. 60090	
A	7/16/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL $\pm 1/64$ ANGULAR: MACH $\pm 1^\circ$ BEND $\pm 1^\circ$ ONE PLACE DECIMAL $\pm .015$ TWO PLACE DECIMAL $\pm .010$ THREE PLACE DECIMAL $\pm .005$	DRAWN JCN	7/13	TITLE: RSSS-313-314-E SERIES	
			INTERPRET GEOMETRIC TOLERANCING PER:	CHECKED		SIZE DWG. NO. <b>A</b> RSSS-313-314-E ASSEMBLY	
			MATERIAL <b>STAINLESS</b>	ENG APPR.		SCALE: 2:3	
			FINISH	MFG APPR.		SHEET 1 OF 1	
			DO NOT SCALE DRAWING	Q.A.			
				<b>PROPRIETARY AND CONFIDENTIAL</b> THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.			

5

4

3

2

1