



316 STAINLESS STEEL AVAILABLE

ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSSS-100-B	BODY	304 STAINLESS	1
2	SRB-103 - SRB-110	BUSHING	NEOPRENE	1
3	SW-100-SS	WASHER	304 STAINLESS	1
4	RSSS-100-N	NUT	304 STAINLESS	1
5	SOR-1-VNT	O-RING	BUNA-N	1
6	LN-50	LOCKNUT	ADD: L, C.R.S. ZINC PLATED	1
7	LNSS-50	LOCKNUT	ADD:LNSS, 316 STAINLESS STEEL	1

CATALOG NUMBER	SEALING RANGE	BODY BORE
RSSS-103	.125 - .188	.610
RSSS-104	.188 - .250	.610
RSSS-105	.250 - .312	.610
RSSS-106	.312 - .375	.610
RSSS-107	.375 - .438	.610
RSSS-108	.438 - .500	.610
RSSS-109	.500 - .562	.610
RSSS-110	.562 - .625	.610

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	REMKE REMKE INDUSTRIES 310 CHADDICK DR, WHEELING, IL. 60090	
A	5/13/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1° BEND ± 1° ONE PLACE DECIMAL ± .015 TWO PLACE DECIMAL ± .010 THREE PLACE DECIMAL ± .005 INTERPRET GEOMETRIC TOLERANCING PER: MATERIAL STAINLESS FINISH DO NOT SCALE DRAWING	DRAWN JCN CHECKED ENG APPR. MFG APPR. Q.A.	5/13	TITLE: RSSS-100 SERIES	
			PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.			SIZE A DWG. NO. RSSS-100 ASSEMBLY	SCALE: 3:2 SHEET 1 OF 1