



ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSR-300-B	BODY	ALUMINUM	1
2	SRB-311 - SRB-312	BUSHING	NEOPRENE	1
3	RSR-300-ND2	NUT	ALUMINUM	1
4	LN-100	LOCK NUT	ADD: L, C.R.S. ZINC PLATED	1
5	R-212-D	MESH	STAINLESS WIRE	1



CATALOG NUMBER	SEALING RANGE	BODY BORE
RSR-311-E	.562 - .688	.990
RSR-312-E	.625 - .750	.990

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	 REMKE INDUSTRIES 310 CHADDICK DR, WHEELING, IL. 60090	
A	7/1/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL $\pm 1/64$ ANGULAR: MACH $\pm 1^\circ$ BEND $\pm 1^\circ$ ONE PLACE DECIMAL $\pm .015$ TWO PLACE DECIMAL $\pm .010$ THREE PLACE DECIMAL $\pm .005$	DRAWN	JCN	7/13	TITLE: RSR-311-312-E SERIES
			INTERPRET GEOMETRIC TOLERANCING PER:	CHECKED			SIZE A DWG. NO. RSR-311-312-E ASSEMBLY
			MATERIAL ALUMINUM	ENG APPR.			
			FINISH	MFG APPR.			SCALE: 2:3 SHEET 1 OF 1
			DO NOT SCALE DRAWING	Q.A.			

5

↑

4

3

2

1